

Eaton M22-LED230H-G

Catalog Number: M22-LED230H-G

Eaton M22 modular pushbutton, LED Light Unit, Screw, IP66, NEMA 4X, 13, Illuminated, Green, 207-264V

Photo is representative



General specifications

Product Name	Catalog Number
Eaton M22 modular pushbutton	M22-LED230H-G
UPC	Product Length/Depth
786685277660	5 in
Product Height	Product Width
0.5 in	3 in
Product Weight	Warranty
0.03 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
Bureau Veritas	CCC Marked
CE Marked	CSA Certified
GoST-R	Lloyd's Register Certified
Catalog Notes	
For complete listing of available button lenses, light units and contact blocks, see Accessories	

Type

Light Unit

Environmental rating

IP66, NEMA 4X, 13

Voltage rating

207-264 V

Illumination

Illuminated

Series

M22

Size

22.5 mm

Actuator

Screw

Light color

Green

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Eaton Specification Sheet - M22-LED230H-G](#)[Global Data Sheet - M22-LED230H-G](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)