

Eaton M22-LEDC230-G

Catalog Number: M22-LEDC230-G

Eaton M22 modular pushbutton, LED Light Unit, Base, Screw, IP66, NEMA 4X, 13, Rk resistance 1, Illuminated, Green, 85-264V

General specifications



Photo is representative

Product Name

Eaton M22 modular pushbutton

Catalog Number

M22-LEDC230-G

UPC

786685277745

Product Length/Depth

1.46 in

Product Height

1.03 in

Product Width

1.18 in

Product Weight

0.026 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

GoST-R

Bureau Veritas

CE Marked

Certifications

CCC Marked

CSA Certified

Lloyd's Register Certified

Type

Light Unit

Environmental rating

IP66, NEMA 4X, 13, Rk resistance 1

Voltage rating

85-264 V

Illumination

Illuminated

Series

M22

Size

22.5 mm

Actuator

Base, screw

Light color

Green

Brochures[M22 Pilot Devices](#)**Catalogs**[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)**Installation instructions**[M22 Operators and Accessories](#)**Specifications and datasheets**[Eaton Specification Sheet - M22-LEDC230-G](#)[Quick Selector - M22 Pushbuttons](#)[Global Data Sheet - M22-LEDC230-G](#)

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)