

Eaton M22-LEDC230H-B

Catalog Number: M22-LEDC230H-B

Eaton M22 modular pushbutton, Blue LED Light Unit, Base mounting, Terminal type: Screw, IP66, NEMA 4X, 13, Rk resistance 1, Illuminated, 207-264V



Photo is representative

General specifications

Product Name

Eaton M22 modular pushbutton

Catalog Number

M22-LEDC230H-B

UPC

786685277790

Product Length/Depth

5 in

Product Height

0.5 in

Product Width

3 in

Product Weight

0.03 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Bureau Veritas

CE Marked

GoST-R

Certifications

CSA Certified

CCC Marked

Lloyd's Register Certified

Type

Light Unit

Environmental rating

IP66, NEMA 4X, 13, Rk resistance 1

Voltage rating

85-264 V

Illumination

Illuminated

Series

M22

Size

22.5 mm

Actuator

Base, screw

Light color

Blue

Brochures

M22 Pilot Devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Installation instructions

M22 Operators and Accessories

Specifications and datasheets

Eaton Specification Sheet - M22-LEDC230H-B

Global Data Sheet - M22-LEDC230H-B



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia