

# Eaton M22-LEDC230H-R

Catalog Number: M22-LEDC230H-R

Eaton M22 modular pushbutton, LED Light Unit, Base, Screw, IP66, NEMA 4X, 13, Rk resistance 10, Illuminated, Red, 85-264V



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton M22 modular pushbutton	M22-LEDC230H-R
<b>UPC</b>	<b>Product Length/Depth</b>
786685277776	0.9 in
<b>Product Height</b>	<b>Product Width</b>
0.35 in	1 in
<b>Product Weight</b>	<b>Warranty</b>
0.028 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Compliances</b>	<b>Certifications</b>
Bureau Veritas	CCC Marked
GoST-R	CSA Certified
CE Marked	Lloyd's Register Certified

Type

Light Unit

Environmental rating

IP66, NEMA 4X, 13, Rk resistance 10

Voltage rating

85-264 V

Illumination

Illuminated

Series

M22

Size

22.5 mm

Actuator

Base, screw

Light color

Red

Brochures

M22 Pilot Devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Installation instructions

M22 Operators and Accessories

Specifications and datasheets

Global Data Sheet - M22-LEDC230H-R

Eaton Specification Sheet - M22-LEDC230H-R



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia