

# Eaton M22-LEDC-B

Catalog Number: M22-LEDC-B

Eaton M22 modular pushbutton, LED Light Unit, Base, Screw, IP66, NEMA 4X, 13, Rk resistance 100, Illuminated, Blue, 12-30 Vac/dc



Photo is representative

## General specifications

### Product Name

Eaton M22 modular pushbutton

### Catalog Number

M22-LEDC-B

### UPC

786685277714

### Product Length/Depth

5 in

### Product Height

0.5 in

### Product Width

3 in

### Product Weight

0.03 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

Bureau Veritas

CE Marked

GoST-R

### Certifications

CSA Certified

CCC Marked

Lloyd's Register Certified

Type

Light Unit

Environmental rating

IP66, NEMA 4X, 13, Rk resistance 100

Voltage rating

12-30 Vac/dc

Illumination

Illuminated

Series

M22

Size

22.5 mm

Actuator

Base, screw

Light color

Blue

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Global Data Sheet - M22-LEDC-B](#)

[Eaton Specification Sheet - M22-LEDC-B](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)