

Eaton M22-LEDC-G

Catalog Number: M22-LEDC-G

Eaton M22 modular pushbutton, LED Light Unit, Base, Screw, IP66, NEMA 4X, 13, Rk resistance 100, Illuminated, Green, 12-30 Vac/dc



General specifications

Product Name

Eaton M22 modular pushbutton

Catalog Number

M22-LEDC-G

UPC

786685277707

Product Length/Depth

1 in

Product Height

0.25 in

Product Width

0.9 in

Product Weight

0.1 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CE Marked

GoST-R

Bureau Veritas

Certifications

CCC Marked

CSA Certified

Lloyd's Register Certified



Powering Business Worldwide

Type

Light Unit

Environmental rating

IP66, NEMA 4X, 13, Rk resistance 100

Voltage rating

12-30 Vac/dc

Illumination

Illuminated

Series

M22

Size

22.5 mm

Actuator

Base, screw

Light color

Green

Brochures

M22 Pilot Devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Installation instructions

M22 Operators and Accessories

Specifications and datasheets

Eaton Specification Sheet - M22-LEDC-G

Global Data Sheet - M22-LEDC-G

Quick Selector - M22 Pushbuttons



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia