

Eaton M22-LED-W

Catalog Number: M22-LED-W

Eaton M22 modular pushbutton, LED Light Unit, Screw, IP66, NEMA 4X, 13, Rk resistance 4.7, Illuminated, White, 12-30 Vac/dc



General specifications

Product Name	Catalog Number
Eaton M22 modular pushbutton	M22-LED-W
UPC	Product Length/Depth
786685277561	2 in
Product Height	Product Width
0.2 in	2 in
Product Weight	Warranty
0.1 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
CE Marked	CSA Certified
Bureau Veritas	CCC Marked
GoST-R	Lloyd's Register Certified

Catalog Notes

For complete listing of available button lenses, light units and contact blocks, seeAccessories

Type

Light Unit

Environmental rating

IP66, NEMA 4X, 13, Rk resistance 4.7

Voltage rating

12-30 Vac/dc

Illumination

Illuminated

Series

M22

Size

22.5 mm

Actuator

Screw

Light color

White

Brochures

M22 Pilot Devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Installation instructions

M22 Operators and Accessories

Specifications and datasheets

Global Data Sheet - M22-LED-W

Eaton Specification Sheet - M22-LED-W



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia