

# Eaton M22-L-X

Catalog Number: M22-L-X

Eaton M22 Flush lensless indicating light operator, Indicating Light, Flush, IP66, NEMA 4X, 13, Rk resistance 47, 22.5 mm, Lensless, Illuminated, White, 100, 000 Hours of operation



## General specifications

### Product Name

Eaton M22 modular pushbutton

### Catalog Number

M22-L-X

### UPC

786685278643

### Product Length/Depth

8 in

### Product Height

0.1 in

### Product Width

5 in

### Product Weight

0.02 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

GoST-R

CE Marked

Bureau Veritas

### Certifications

CSA Certified

CCC Marked

Lloyd's Register Certified

### Catalog Notes

Includes contact block mounting adapter.

## Type

Indicating Light

## Environmental rating

IP66, NEMA 4X, 13, Rk resistance 47

## Operating Cycles

100,000 Hours of operation

## Illumination

Illuminated

## Series

M22

## Size

22.5 mm

## Actuator

Flush

## Button color

Lensless

## Light color

White

## Brochures

[M22 Pilot Devices](#)

## Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

## Drawings

[M22-L-X 3D Inventor](#)[M22-L-X 2D PDF](#)[M22-L-X AutoCAD 2D Footprint](#)[M22-L-X 2D Drawing Xchange](#)[M22-L-X 3D Model Xchange](#)[M22-L-X AutoCAD 2D Footprint \(mm\)](#)

## Installation instructions

[M22 Operators and Accessories](#)

## Specifications and datasheets

[Global Data Sheet - M22-L-X](#)[Eaton Specification Sheet - M22-L-X](#)

Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)