

Eaton M22-L-Y

Catalog Number: M22-L-Y

Eaton M22 modular pushbutton, Indicating Light Operator, Flush, IP66, NEMA 4X, 13, Rk resistance 470, 22.5 mm, Yellow, Illuminated, White, 100, 000 Hours of operation



General specifications

Product Name

Eaton M22 modular pushbutton

UPC

786685278650

Product Height

1 in

Product Weight

0.1 lb

Catalog Number

M22-L-Y

Product Length/Depth

2 in

Product Width

2 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Bureau Veritas
CE Marked
GoST-R

Certifications

CCC Marked
CSA Certified
Lloyd's Register Certified

Catalog Notes

Includes contact block mounting adapter.

Type

Indicating Light

Environmental rating

IP66, NEMA 4X, 13, Rk resistance 470

Operating Cycles

100,000 Hours of operation

Illumination

Illuminated

Series

M22

Size

22.5 mm

Actuator

Flush

Button color

Yellow

Light color

White

Brochures

M22 Pilot Devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Drawings

M22-L 3D Model Xchange

M22-L 2D Drawing Xchange

M22-L AutoCAD 2D Footprint (mm)

M22-L 2D PDF

M22-L AutoCAD 2D Footprint

M22-L 3D Inventor

Installation instructions

M22 Operators and Accessories

Specifications and datasheets

Eaton Specification Sheet - M22-L-Y

Global Data Sheet - M22-L-Y



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia