

# Eaton M22M-DL-G-K20-230G

Catalog Number: M22M-DL-G-K20-230G

Eaton M22 modular pushbutton, 22.5 mm, Metal, Illuminated flush momentary, Green lens, 2NO, Green light units, 85-264 Vac/dc, NEMA 4x, 13, IP67, IP69K (IP66 key-release)

## General specifications



### Product Name

Eaton M22 modular pushbutton

### Catalog Number

M22M-DL-G-K20-230G

### UPC

786685861357

### Product Length/Depth

1.17 in

### Product Height

1.17 in

### Product Width

0.39 in

### Product Weight

0.01 lb

### Certifications

Contact Manufacturer

Photo is representative

## defaultTaxonomyAttributeLabel

### Application

Pushbutton

### Special features

M22 series

### Type

22.5 mm RMQ-Titan Modular

### Bezel

Metal

### Actuator function

Momentary

### Enclosure

NEMA 13

NEMA 4X

### Button color

Green

### Actuator

Flush

### Operating mode

Momentary

### Contact configuration

2 NO

### Illumination

Illuminated

### Series

M22

### Environmental rating

IP67, IP69K (IP66 key-release)

### Light unit voltage

85-264 Vac/dc

### Light color

Green

### Size

22.5 mm

## Resources

### Brochures

[M22 Pilot Devices](#)

### Specifications and datasheets

[Eaton Specification Sheet - M22M-DL-G-K20-230G](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)