

# Eaton M22M-DLH-W

Catalog Number: M22M-DLH-W

Eaton M22 modular pushbutton, 22.5 mm, Metal, Illuminated extended momentary, White lens, NEMA 4x, 13, IP67, IP69K (IP66 key-release)

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton M22 modular pushbutton	M22M-DLH-W
<b>UPC</b>	<b>Product Length/Depth</b>
786685861777	1.17 in
<b>Product Height</b>	<b>Product Width</b>
1.17 in	0.39 in
<b>Product Weight</b>	<b>Certifications</b>
0.01 lb	Contact Manufacturer

## defaultTaxonomyAttributeLabel

### Application

Pushbutton

### Special features

M22 series

### Type

22.5 mm RMQ-Titan Modular

### Bezel

Metal

### Actuator function

Momentary

### Enclosure

NEMA 4X

NEMA 13

### Actuator

Flush

### Operating mode

Momentary

### Illumination

Illuminated

### Series

M22

### Environmental rating

IP67, IP69K (IP66 key-release)

### Size

22.5 mm

## Resources

### Brochures

M22 Pilot Devices

### Drawings

M22(S)(M)-DLH 2D Drawing Xchange

M22(S)(M)-DLH 2D PDF

M22(S)(M)-DLH AutoCAD 2D Footprint

M22(S)(M)-DLH 3D Model Xchange

M22(S)(M)-DLH AutoCAD 2D Footprint (mm)

M22(S)(M)-DLH 3D Inventor

### Specifications and datasheets

Eaton Specification Sheet - M22M-DLH-W