

Eaton M22M-DL-R-K11-R

Catalog Number: M22M-DL-R-K11-R

Eaton M22 modular pushbutton, 22.5 mm, Metal, Illuminated flush momentary, Red lens, 1NO-1NC, 12-30 Vac/dc, NEMA 4x, 13, IP67, IP69K (IP66 key-release)

General specifications



Product Name

Eaton M22 modular pushbutton

Catalog Number

M22M-DL-R-K11-R

UPC

786685861241

Product Length/Depth

1.17 in

Product Height

1.17 in

Product Width

0.39 in

Product Weight

0.01 lb

Certifications

Contact Manufacturer

Photo is representative

defaultTaxonomyAttributeLabel

Application

Pushbutton

Special features

M22 series

Type

22.5 mm RMQ-Titan Modular

Bezel

Metal

Actuator function

Momentary

Enclosure

NEMA 4X

NEMA 13

Button color

Red

Actuator

Flush

Operating mode

Momentary

Contact configuration

1 NO-1 NC

Illumination

Illuminated

Series

M22

Environmental rating

IP67, IP69K (IP66 key-release)

Light unit voltage

12-30 Vac/dc

Light color

Red

Size

22.5 mm

Resources

Brochures

[M22 Pilot Devices](#)

Specifications and datasheets

[Eaton Specification Sheet - M22M-DL-R-K11-R](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)