

Eaton M22M-DRL-W-K01-W

Catalog Number: M22M-DRL-W-K01-W

Eaton M22 modular pushbutton, 22.5 mm, Illuminated, Metal, Maintained, White, 1NC, White, 12-30 Vac/dc, NEMA 4x, 13, IP67, IP69K (IP66 key-release)

General specifications



Photo is representative

Product Name	Catalog Number
Eaton M22 modular pushbutton	M22M-DRL-W-K01-W
UPC	Product Length/Depth
786685861623	1.17 in
Product Height	Product Width
1.17 in	0.39 in
Product Weight	Compliances
0.01 lb	CE Marked

defaultTaxonomyAttributeLabel

Application

Pushbutton

Special features

M22 series

Type

22.5 mm RMQ-Titan Modular

Bezel

Metal

Actuator function

Momentary

Enclosure

NEMA 13

NEMA 4X

Button color

White

Actuator

Flush

Operating mode

Maintained

Contact configuration

1 NC

Illumination

Illuminated

Series

M22

Environmental rating

IP67, IP69K (IP66 key-release)

Light unit voltage

12-30 Vac/dc

Light color

White

Size

22.5 mm

Resources

Brochures

[M22 Pilot Devices](#)

Specifications and datasheets

[Eaton Specification Sheet - M22M-DRL-W-K01-W](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)