

# Eaton M22M-DRL-Y-K10-W

Catalog Number: M22M-DRL-Y-K10-W

Eaton M22 modular pushbutton, 22.5 mm, Illuminated, Metal, flush maintained, Yellow, 1NO, White, 12-30 Vac/dc, NEMA 4x, 13, IP67, IP69K (IP66 key-release)

## General specifications



Product Name	Eaton M22 modular pushbutton	Catalog Number	M22M-DRL-Y-K10-W
UPC	786685861722	Product Length/Depth	1.17 in
Product Height	1.17 in	Product Width	0.39 in
Product Weight	0.01 lb	Compliances	CE Marked

Photo is representative

## defaultTaxonomyAttributeLabel

### Application

Pushbutton

### Special features

M22 series

### Type

22.5 mm RMQ-Titan Modular

### Bezel

Metal

### Actuator function

Momentary

### Enclosure

NEMA 13

NEMA 4X

### Button color

Yellow

### Actuator

Flush

### Operating mode

Flush maintained

### Contact configuration

1 NO

### Illumination

Illuminated

### Series

M22

### Environmental rating

IP67, IP69K (IP66 key-release)

### Light unit voltage

12-30 Vac/dc

### Light color

White

### Size

22.5 mm

## Resources

### Brochures

[M22 Pilot Devices](#)

### Specifications and datasheets

[Eaton Specification Sheet - M22M-DRL-Y-K10-W](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)