

# Eaton M22MS-D-G

Catalog Number: M22MS-D-G

Eaton 22.5 mm RMQ-Titan Pushbutton, Green Actuator, Black Metal bezel, IP67, IP69K, Non-illuminated, Flush mounting, NEMA 4X, 13,5,000,000 operations, Momentary, 22.5 mm, Flush Pushbutton, M22

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton M22 modular pushbutton	M22MS-D-G
<b>UPC</b>	<b>Product Length/Depth</b>
790500000364	17.716 in
<b>Product Height</b>	<b>Product Width</b>
36.023 in	35.629 in
<b>Product Weight</b>	<b>Compliances</b>
11.0232 lb	Bureau Veritas CE Marked GoST-R

**Certifications**  
CSA Certified  
CCC Marked  
Lloyd's Register Certified

## defaultTaxonomyAttributeLabel

### Type

Modular pushbutton

### Actuator color

Green

### Bezel

Metal

### Enclosure

IP69K

IP67

### Operating mode

Momentary

### Illumination

Non-illuminated

### Series

M22

### Operating cycles

5 million

### Mounting method

Flush

### Degree of protection

NEMA 13

NEMA 4X

### Product category

Flush pushbutton

### Size

22.5 mm

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - M22MS-D-G](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)