

Eaton M22S-DDLF-GR-X1-X0

Catalog Number: M22S-DDLF-GR-X1-X0

Eaton M22 Modular Double Pushbutton Operator Only, 22.5 mm, Flush, Momentary, Illuminated, Bezel: Black, Button: Top Green, Bottom Red, Inscription: Top I, Bottom O/ X1, X0, IP66, NEMA 4X, 13, Light 100,000 hours, Button 200,000 Operations



Photo is representative

General specifications

Product Name	Catalog Number
Eaton M22 pushbutton operator	M22S-DDLF-GR-X1-X0
UPC	Product Length/Depth
786685271972	7 in
Product Height	Product Width
1.5 in	5 in
Product Weight	Warranty
0.05 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
CE Marked	CCC Marked
GoST-R	CSA Certified
Bureau Veritas	Lloyd's Register Certified
Catalog Notes	
Includes contact block mounting adapter.	

defaultTaxonomyAttributeLabel

Type

Double Pushbutton with Center Light

Bezel

Black

Actuator function

Momentary

Button color

Top: green, bottom: red

Actuator

Flush, dual button

Illumination

Illuminated

Series

M22

Environmental rating

IP66, NEMA 4X, NEMA 13

Etching code

X1, X0

Operating cycles

Light: 100,000, button: 200,000

Inscription

Top I, Bottom O

Size

22.5 mm

Resources

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Eaton Specification Sheet - M22S-DDLF-GR-X1-X0](#)

[Global Data Sheet - M22S-DDLF-GR-X1-X0](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)