

Eaton M22S-DDLM-GR

Catalog Number: M22S-DDLM-GR

Eaton M22 pushbutton Op,MIXED ILL DBL PB BLK-BZL GRN TOP RED BTM,Modular Double Pushbutton Op Only,22.5mm,Top Flush,Bottom Ext,Momentary,Illum,Bezel: Black,Button: Top Green,Bottom Red,IP66,NEMA 4X,13,Light 100k hours,Button 200k Oper



Photo is representative

General specifications

Product Name	Catalog Number
Eaton M22 pushbutton operator	M22S-DDLM-GR
UPC	Product Length/Depth
786685272054	7 in
Product Height	Product Width
1.5 in	5 in
Product Weight	Warranty
0.05 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
GoST-R	CCC Marked
CE Marked	CSA Certified
Bureau Veritas	Lloyd's Register Certified

Catalog Notes

Includes contact block mounting adapter.

defaultTaxonomyAttributeLabel

Type

Double Pushbutton with Center Light

Bezel

Black

Actuator function

Momentary

Button color

Top: green, bottom: red

Actuator

Top flush, bottom extended, dual button

Illumination

Illuminated

Series

M22

Environmental rating

IP66, NEMA 4X, NEMA 13

Operating cycles

Light: 100,000, button: 200,000

Size

22.5 mm

Resources

Specifications and datasheets

[Eaton Specification Sheet - M22S-DDLM-GR](#)

[Global Data Sheet - M22S-DDLM-GR](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)