

# Eaton M22S-WRLK-G

Catalog Number: M22S-WRLK-G

Eaton M22 modular pushbutton, M22 Modular Selector Switch Operator, 22.5 mm, Knob, Maintained, Illuminated, Bezel: Black, Button: Green, IP66, NEMA 4X, 13, Two-position, Light 100,000 hours, Button 100,000 Operations



Photo is representative

## General specifications

|                                          |                                                                                                                                                                                  |
|------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product Name</b>                      | <b>Catalog Number</b>                                                                                                                                                            |
| Eaton M22 modular pushbutton             | M22S-WRLK-G                                                                                                                                                                      |
| <b>UPC</b>                               | <b>Product Length/Depth</b>                                                                                                                                                      |
| 786685281216                             | 1.17 in                                                                                                                                                                          |
| <b>Product Height</b>                    | <b>Product Width</b>                                                                                                                                                             |
| 1.06 in                                  | 1.17 in                                                                                                                                                                          |
| <b>Product Weight</b>                    | <b>Warranty</b>                                                                                                                                                                  |
| 0.05 lb                                  | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| <b>Compliances</b>                       | <b>Certifications</b>                                                                                                                                                            |
| CE Marked<br>Bureau Veritas<br>GoST-R    | CCC Marked<br>CSA Certified<br>Lloyd's Register Certified                                                                                                                        |
| <b>Catalog Notes</b>                     |                                                                                                                                                                                  |
| Includes contact block mounting adapter. |                                                                                                                                                                                  |

defaultTaxonomyAttributeLabel

Type

Selector switch

Bezel

Black

Actuator function

Maintained

Button color

Green

Actuator

Knob

Environmental rating

IP66, NEMA 4X, NEMA 13

Illumination

Illuminated

Number of positions

2

Operating cycles

Light: 100,000, button: 100,000

Series

M22

Size

22.5 mm

Resources

Brochures

M22 Pilot Devices

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Specifications and datasheets

Eaton Specification Sheet - M22S-WRLK-G

Global Data Sheet - M22S-WRLK-G



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
  
All other trademarks are property of their respective owners.



Eaton.com/socialmedia