

Eaton M22S-WS-MS6

Catalog Number: M22S-WS-MS6

Eaton M22 Modular Two Position Key-Operated Selector Switch, 22.5 mm, Momentary, Return from right, key removable left, Non-illuminated, Bezel: Black, Button: Black, MS6, IP66, NEMA 4X, 13, Two-position, 100,000 Operations

General specifications



Photo is representative

Product Name

Eaton M22 modular pushbutton

Catalog Number

M22S-WS-MS6

UPC

786685280516

Product Length/Depth

7 in

Product Height

1.5 in

Product Width

5 in

Product Weight

0.13 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CE Marked
Bureau Veritas
GoST-R

Certifications

CSA Certified
CCC Marked
Lloyd's Register Certified

Catalog Notes

Includes one key and one contact block mounting adapter. Removal positions can be modified in the field using coding adapters.

defaultTaxonomyAttributeLabel

Type

Selector switch

Bezel

Black

Operating Cycles

100,000 operations

Actuator function

Momentary, Return from right, key removable left

Button color

Black

Actuator

Key operated

Size

22.5 mm

Environmental rating

IP66, NEMA 4X, NEMA 13

Illumination

Non-illuminated

Key code

MS6

Number of positions

2

Series

M22

Resources

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Specifications and datasheets

[Global Data Sheet - M22S-WS-MS6](#)

[Eaton Specification Sheet - M22S-WS-MS6](#)