

# Eaton M22-W

Catalog Number: M22-W

Eaton M22 pushbutton operator, 22.5 mm, Rotary, Momentary, Non-illuminated, Bezel: Silver, Button: Black, Inscription: I, 0/ X1, X0, IP66, NEMA 4X, 13, Two-position, 100,000 Operations



## General specifications

### Product Name

Eaton M22 pushbutton operator

### Catalog Number

M22-W

### UPC

786685281391

### Product Length/Depth

7 in

### Product Height

1.5 in

### Product Width

5 in

### Product Weight

0.99 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

Bureau Veritas

CE Marked

GoST-R

### Certifications

CSA Certified

CCC Marked

Lloyd's Register Certified

### Catalog Notes

Includes contact block mounting adapter.

Can be converted in the field to maintained operation with the removal of a color coded adapter.

## defaultTaxonomyAttributeLabel

### Type

Selector switch

### Bezel

Silver

### Actuator function

Momentary

### Button color

Black

### Actuator

Rotary

### Environmental rating

IP66, NEMA 4X, NEMA 13

### Etching code

X1, X0

### Illumination

Non-illuminated

### Inscription

I, 0

### Number of positions

2

### Operating cycles

100,000

### Series

M22

### Size

22.5 mm

## Resources

### Brochures

[M22 Pilot Devices](#)

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Installation instructions

[M22 Operators and Accessories](#)

### Specifications and datasheets

[Eaton Specification Sheet - M22-W](#)

[Global Data Sheet - M22-W](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)