

# Eaton M22-WLK3-Y

Catalog Number: M22-WLK3-Y

Eaton M22 modular pushbutton, M22 Modular Selector Switch Operator, 22.5 mm, Knob, Momentary, Illuminated, Bezel: Silver, Button: Yellow, IP66, NEMA 4X, 13, Three-position, Light 100,000 hours, Button 100,000 Operations



## General specifications

### Product Name

Eaton M22 modular pushbutton

### Catalog Number

M22-WLK3-Y

### UPC

786685281513

### Product Length/Depth

1.17 in

### Product Height

1.06 in

### Product Width

1.17 in

### Product Weight

0.05 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

Bureau Veritas

GoST-R

CE Marked

### Certifications

CSA Certified

CCC Marked

Lloyd's Register Certified

### Catalog Notes

Includes contact block mounting adapter.

Can be converted in the field to maintained operation with the removal of a color coded adapter.

## defaultTaxonomyAttributeLabel

### Type

Selector switch

### Bezel

Silver

### Actuator function

Momentary

### Button color

Yellow

### Actuator

Knob

### Environmental rating

IP66, NEMA 4X, NEMA 13

### Illumination

Illuminated

### Number of positions

3

### Operating cycles

Light: 100,000, button: 100,000

### Series

M22

### Size

22.5 mm

## Resources

### Brochures

[M22 Pilot Devices](#)

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Installation instructions

[M22 Operators and Accessories](#)

### Specifications and datasheets

[Eaton Specification Sheet - M22-WLK3-Y](#)

[Global Data Sheet - M22-WLK3-Y](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)