

Eaton M22-WLKV-R

Catalog Number: M22-WLKV-R

Eaton M22 modular pushbutton, M22 Modular Selector Switch Operator, 22.5 mm, Knob, Momentary, Illuminated, Bezel: Silver, Button: Red, IP66, NEMA 4X, 13, Two-Position, V, Light 100,000 hours, Button 100,000 Operations

General specifications



Photo is representative

Product Name

Eaton M22 modular pushbutton

UPC

786685281575

Product Height

1.06 in

Product Weight

0.05 lb

Compliances

GoST-R

CE Marked

Bureau Veritas

Catalog Number

M22-WLKV-R

Product Length/Depth

1.17 in

Product Width

1.17 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

CCC Marked

CSA Certified

Lloyd's Register Certified

Catalog Notes

Includes contact block mounting adapter.

Can be converted in the field to maintained operation with the removal of a color coded adapter.

defaultTaxonomyAttributeLabel

Type

Selector switch

Bezel

Silver

Actuator function

Momentary

Button color

Red

Actuator

Knob

Environmental rating

IP66, NEMA 4X, NEMA 13

Illumination

Illuminated

Number of positions

2, Vertical

Operating cycles

Light: 100,000, button: 100,000

Series

M22

Size

22.5 mm

Resources

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Eaton Specification Sheet - M22-WLKV-R](#)

[Global Data Sheet - M22-WLKV-R](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)