

Eaton M22-WRLK3-1-Y

Catalog Number: M22-WRLK3-1-Y

Eaton M22 modular pushbutton, M22 Modular Selector Switch Operator, 22.5 mm, Knob, Maintained, Return from right, Illuminated, Bezel: Silver, Button: Yellow, IP66, NEMA 4X, 13, Three-position, Light 100,000 hours, Button 100,000 Operations



Photo is representative

General specifications

Product Name	Catalog Number
Eaton M22 modular pushbutton	M22-WRLK3-1-Y
UPC	Product Length/Depth
786685281926	1.17 in
Product Height	Product Width
1.06 in	1.17 in
Product Weight	Warranty
0.05 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Compliances	Certifications
CE Marked	CCC Marked
GoST-R	CSA Certified
Bureau Veritas	Lloyd's Register Certified
Catalog Notes	
Includes contact block mounting adapter.	

defaultTaxonomyAttributeLabel

Type

Selector switch

Bezel

Silver

Actuator function

Maintained, return from right

Button color

Yellow

Actuator

Knob

Environmental rating

IP66, NEMA 4X, NEMA 13

Illumination

Illuminated

Number of positions

3

Operating cycles

Light: 100,000, button: 100,000

Series

M22

Size

22.5 mm

Resources

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Eaton Specification Sheet - M22-WRLK3-1-Y](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)