

# Eaton M22-WS3

Catalog Number: M22-WS3

Eaton M22 Modular three position key-operated selector switch, 22.5 mm, Momentary, Return from left/right, key removable center, Non-illuminated, Bezel: Silver, Button: Black, MS1, IP66, NEMA 4X, 13, Three-position, 100,000 Operations



## General specifications

### Product Name

Eaton M22 modular pushbutton

### Catalog Number

M22-WS3

### UPC

786685280226

### Product Length/Depth

3 in

### Product Height

4 in

### Product Width

4 in

### Product Weight

0.13 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

Bureau Veritas

GoST-R

CE Marked

### Certifications

CSA Certified

CCC Marked

Lloyd's Register Certified

### Catalog Notes

Includes one key and one contact block mounting adapter. Removal positions can be modified in the field using coding adapters.

## defaultTaxonomyAttributeLabel

### Type

Selector switch

### Bezel

Silver

### Operating Cycles

100,000 operations

### Actuator function

Momentary, return from left/right, key removable center

### Button color

Black

### Actuator

Key operated

### Size

22.5 mm

### Environmental rating

IP66, NEMA 4X, NEMA 13

### Illumination

Non-illuminated

### Key code

MS1

### Number of positions

3

### Series

M22

## Resources

### Brochures

[M22 Pilot Devices](#)

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Installation instructions

[M22 Operators and Accessories](#)

### Specifications and datasheets

[Global Data Sheet - M22-WS3](#)

[Eaton Specification Sheet - M22-WS3](#)