

Eaton M22-WS3-MS7

Catalog Number: M22-WS3-MS7

Eaton M22 Modular Three Position Key-Operated Selector Switch, 22.5 mm, Momentary, Return from left/right, key removable center, Non-illuminated, Bezel: Silver, Button: Black, MS7, IP66, NEMA 4X, 13, Three-position, 100,000 Operations



Photo is representative

General specifications

Product Name

Eaton M22 modular pushbutton

Catalog Number

M22-WS3-MS7

UPC

786685280288

Product Length/Depth

7 in

Product Height

1.5 in

Product Width

5 in

Product Weight

0.13 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CE Marked
GoST-R
Bureau Veritas

Certifications

CSA Certified
CCC Marked
Lloyd's Register Certified

Catalog Notes

Includes one key and one contact block mounting adapter. Removal positions can be modified in the field using coding adapters.

defaultTaxonomyAttributeLabel

Type

Selector switch

Bezel

Silver

Operating Cycles

100,000 operations

Actuator function

Momentary, return from left/right, key removable center

Button color

Black

Actuator

Key operated

Size

22.5 mm

Environmental rating

IP66, NEMA 4X, NEMA 13

Illumination

Non-illuminated

Key code

MS7

Number of positions

3

Series

M22

Resources

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Eaton Specification Sheet - M22-WS3-MS7](#)

[Global Data Sheet - M22-WS3-MS7](#)