

Eaton M22-WS-MS2

Catalog Number: M22-WS-MS2

Eaton M22 Modular Two Position Key-Operated Selector Switch, 22.5 mm, Momentary, Return from right, key removable left, Non-illuminated, Bezel: Silver, Button: Black, MS2, IP66, NEMA 4X, 13, Two-position, 100,000 Operations

General specifications



Photo is representative

Product Name

Eaton M22 modular pushbutton

UPC

786685280714

Product Height

1.5 in

Product Weight

0.13 lb

Compliances

CE Marked
Bureau Veritas
GoST-R

Catalog Notes

Includes one key and one contact block mounting adapter. Removal positions can be modified in the field using coding adapters.

Catalog Number

M22-WS-MS2

Product Length/Depth

7 in

Product Width

5 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

CCC Marked
CSA Certified
Lloyd's Register Certified

defaultTaxonomyAttributeLabel

Type

Selector switch

Bezel

Silver

Operating Cycles

100,000 operations

Actuator function

Momentary, Return from right, key removable left

Button color

Black

Actuator

Key operated

Size

22.5 mm

Environmental rating

IP66, NEMA 4X, NEMA 13

Illumination

Non-illuminated

Key code

MS2

Number of positions

2

Series

M22

Resources

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Eaton Specification Sheet - M22-WS-MS2](#)

[Global Data Sheet - M22-WS-MS2](#)