

Eaton M22-XDH-G-GB1

Catalog Number: M22-XDH-G-GB1

Eaton M22 pushbutton button plate, M22 Button Plate, 22.5 mm, Extended, Non-illuminated, Button: freen, Inscription: START/ GB1, IP67, IP69K, NEMA 4X, 21

General specifications



Photo is representative

Product Name

Eaton M22 pushbutton button plate

Catalog Number

M22-XDH-G-GB1

UPC

786685272856

Product Length/Depth

1 in

Product Height

0.26 in

Product Width

1 in

Product Weight

0.009 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

GoST-R

CE Marked

Bureau Veritas

Certifications

CSA Certified

CCC Marked

Lloyd's Register Certified

Type

Button plate

Button color

Green

Actuator

Extended

Illumination

Non-illuminated

Series

M22

Inscription

START

Environmental rating

IP67, IP69K, NEMA 4X, NEMA 21

Etching code

GB1

Size

22.5 mm

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Global Data Sheet - M22-XDH-G-GB1](#)[Eaton Specification Sheet - M22-XDH-G-GB1](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)