

# Eaton MBE1224B125BTS

Catalog Number: MBE1224B125BTS

Eaton Meter Breaker EUSERC Type BR , BR2125 main breaker, 125A, 120/240V, Ring,12 spaces,24 circuits,10 kAIC,Surface mounting,Box size A, Aluminum bus, Overhead/underground feed, Four-jaws, 1 socket, #6-250 kcmil line, #14-2/0 AWG ground



## General specifications

Product Name	Catalog Number
Eaton meter breaker EUSERC	MBE1224B125BTS
UPC	Product Length/Depth
782114890813	5.38 in
Product Height	Product Width
23.88 in	14.44 in
Product Weight	Warranty
40 lb	10 year
Compliances	Certifications
EUSERC Approved	UL Listed

## defaultTaxonomyAttributeLabel

### Type

All-in-ones

### Utility approvals

AZ : Arizona Public Service Company

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

ID : Idaho Power

OR : Idaho Power

WA : Seattle City Light

AK : Anchorage Municipal Light & Power

NV : NV Energy

CA : City of Los Angeles - DWP (LADWP)

AZ : Southern California Edison

CA : Southern California Edison

CA : Pacific Gas and Electric (PG&E)

CA : Sacramento Municipal Utility District (SMUD)

AZ : Salt River Project (SRP)

HI : Hawaiian Electric

MT : NorthWestern Energy

NE : NorthWestern Energy

SD : NorthWestern Energy

WY : NorthWestern Energy

AZ : Tucson Electric Power/ UniSource

AZ : Sulphur Springs Valley Electric Coop

WA : Puget Sound Energy

WA : Tacoma Public Utilities

### Interrupt rating

10 kAIC

### Box size

A

### Enclosure

NEMA 3R

### Ground

#14-2/0 AWG

### Voltage rating

120/240 V

### Number of sockets

1

## Resources

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - METER BREAKER WEST COAST STYLE V1

### Specifications and datasheets

Technical Data Residential Meter Breakers: Type CH and BR Residential

Eaton Specification Sheet - MBE1224B125BTS

Phase

Single-phase

Used with

Type BR breakers

Number of circuits

24

Bus material

Aluminum

Feed type

Top/bottom

Main circuit breaker

BR2125

Number of jaws

Four-jaw



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)