

Eaton MBE2040B200BTS

Catalog Number: MBE2040B200BTS

Eaton Meter Breaker EUSERC Type BR , CSR2200 main breaker, 200A, 120/240V, Ring, 20 spaces, 40 circuits, 22 kAIC, Surface mounting, Box size A, Aluminum bus, OH/UG feed, Four-jaws, 1 socket, #6-250 kcmil line, #6-250 kcmil ground



General specifications

Product Name	Catalog Number
Eaton meter breaker EUSERC	MBE2040B200BTS
UPC	Product Length/Depth
782114883594	5.5 in
Product Height	Product Width
36.06 in	16.63 in
Product Weight	Warranty
46.25 lb	10 year
Compliances	Certifications
EUSERC Approved	UL Listed

defaultTaxonomyAttributeLabel

Type

All-in-ones

Utility approvals

ID : Avista Utilities

WA : Avista Utilities

NM : El Paso Electric

TX : El Paso Electric

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

ID : Idaho Power

OR : Idaho Power

WA : Seattle City Light

AK : Anchorage Municipal Light & Power

NV : NV Energy

CA : City of Los Angeles - DWP (LADWP)

AZ : Southern California Edison

CA : Southern California Edison

CA : Pacific Gas and Electric (PG&E)

CA : Sacramento Municipal Utility District (SMUD)

AZ : Salt River Project (SRP)

HI : Hawaiian Electric

MT : NorthWestern Energy

NE : NorthWestern Energy

SD : NorthWestern Energy

WY : NorthWestern Energy

AZ : Tucson Electric Power/ UniSource

AZ : Sulphur Springs Valley Electric Coop

WA : Puget Sound Energy

WA : Tacoma Public Utilities

Interrupt rating

10 kAIC

22 kAIC

Box size

A

Enclosure

NEMA 3R

Ground

#6-250 kcmil

Voltage rating

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - MBE2040B225BTS, BTF - MBE2040B200BTS, BTF

Specifications and datasheets

Eaton Specification Sheet - MBE2040B200BTS

Technical Data Residential Meter Breakers: Type CH and BR Residential

120/240 V

Number of sockets

1

Phase

Single-phase

Used with

Type BR breakers

Number of circuits

40

Bus material

Aluminum

Feed type

Top/bottom

Main circuit breaker

CSR2200

Number of jaws

Four-jaw



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia