

Eaton MD075E67ES

Catalog Number: MD075E67ES

Drive Isolation Transformer, Ventilated, Dry Type Distribution, DT-3, Three-phase, PV: 380 delta, Taps: 1 at +5% FCAN, 1 at -5% FCBN, SV: 380Y/220, 150°C, 7.5 kVA, Al windings, Elec. Shield, Frame: 912B, uses WS38



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Motor drive isolation ventilated transformer	MD075E67ES
	UPC
	786680058660
Product Length/Depth	Product Height
16.5 in	30 in
Product Width	Product Weight
23 in	196 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

DT-3

Frame

912B

Tap size

1 at +5% FCAN, 1 at -5% FCBN

Type

Dry Type Distribution, Drive Isolation Transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

7.5 kVA

Phase

Three-phase

Primary voltage

380 V

Secondary Voltage

380Y/220 V

Temperature rise

150 °C rise

Miscellaneous

Special features

Electrostatically shielded

Weathershield

WS38

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - MD075E67ES](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)