

Eaton MD118E73NV

Catalog Number: MD118E73NV

Drive Isolation Transformer, Ventilated, Dry Type Distribution, DT-3, Three-phase, PV: 460 delta, Taps: 1 at +5% FCAN, 1 at -5% FCBN, SV: 460 delta, 150°C, 11 kVA, Al windings, Frame: 917N



Photo is representative

General specifications

Product Name

Eaton Totally enclosed non-ventilated transformer

Catalog Number

MD118E73NV

UPC

786680053191

Product Length/Depth

24.67 in

Product Height

56.18 in

Product Width

31.44 in

Product Weight

1262 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Totally enclosed non-ventilated DS-3 or DT-3



Powering Business Worldwide

Physical Attributes

Coil material

Aluminum

Design

DT-3

Frame

917N

Tap size

1 at +5% FCAN, 1 at -5% FCBN

Type

Dry Type Distribution, Drive Isolation Transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

11 kVA

Phase

Three-phase

Primary voltage

460 V

Secondary Voltage

460 V

Temperature rise

150 °C rise

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - MD118E73NV](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)