

Eaton MD118E87

Catalog Number: MD118E87

Drive Isolation Transformer, Ventilated, Dry Type Distribution, DT-3, Three-phase, PV: 208 delta, Taps: 1 at +5% FCAN, 1 at -5% FCBN, SV: 480 delta, 150°C, 11 kVA, Al windings, Frame: 916A, uses WS19



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Motor drive isolation ventilated transformer	MD118E87
	UPC
	786680056697
Product Length/Depth	Product Height
23.42 in	48.56 in
Product Width	Product Weight
28.22 in	942 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

DT-3

Frame

916A

Tap size

1 at +5% FCAN, 1 at -5% FCBN

Type

Dry Type Distribution, Drive Isolation Transformer

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

208 V

Secondary Voltage

480 V

Temperature rise

150 °C rise

Volt ampere rating

11 kVA

Miscellaneous

Weathershield

WS19

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - MD118E87](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)