

Eaton MD14E88ZZ

Catalog Number: MD14E88ZZ

Drive Isolation Transformer, Ventilated, Dry Type Distribution, DT-3, Three-phase, PV: 230 delta, Taps: 1 at +5% FCAN, 1 at -5% FCBN, SV: 230Y/133V, 150°C, 14 kVA, Al windings, Frame: 908S



Photo is representative

General specifications

Product Name

Eaton Open core-coil ventilated transformer

Catalog Number

MD14E88ZZ

UPC

786680056192

Product Length/Depth

14.12 in

Product Height

30 in

Product Width

20.12 in

Product Weight

164 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Recognized from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Open type core and coil assembly

Physical Attributes

Coil material

Aluminum

Design

DT-3

Frame

908S

Tap size

1 at +5% FCAN, 1 at -5% FCBN

Type

Dry Type Distribution, Drive Isolation Transformer

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

230 V

Secondary Voltage

230Y/133 V

Temperature rise

150 °C rise

Volt ampere rating

14 kVA

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - MD14E88ZZ](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)