

# Eaton MD175E73NV

Catalog Number: MD175E73NV

Drive Isolation Transformer, Ventilated, Dry Type Distribution, DT-3, Three-phase, PV: 460 delta, Taps: 1 at +5% FCAN, 1 at -5% FCBN, SV: 460 delta, 150°C, 175 kVA, Al windings, Frame: 918AN



Photo is representative

## General specifications

### Product Name

Eaton Totally enclosed non-ventilated transformer

### Catalog Number

MD175E73NV

### UPC

786680053184

### Product Length/Depth

30.68 in

### Product Height

62.18 in

### Product Width

31.44 in

### Product Weight

1525 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

### Catalog Notes

Totally enclosed non-ventilated DS-3 or DT-3

## Physical Attributes

### Coil material

Aluminum

### Design

DT-3

### Frame

918AN

### Tap size

1 at +5% FCAN, 1 at -5% FCBN

### Type

Dry Type Distribution, Drive Isolation Transformer

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Three-phase

### Primary voltage

460 V

### Secondary Voltage

460 V

### Temperature rise

150 °C rise

### Volt ampere rating

175 kVA

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - MD175E73NV](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)