

Eaton MD175E79

Catalog Number: MD175E79

Dry Type Distribution Motor Drive Isolation Transformer DT-3
Three-phase 480 DELTA 1 at +5% FCAN 1 at -5% FCBN
480Y/277V 150°C 175 kVA Aluminum windings 917 318H WS34
60 Hz 150 hp



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Motor drive isolation ventilated transformer	MD175E79
	UPC
	786680099793
Product Length/Depth	Product Height
24.67 in	56.17 in
Product Width	Product Weight
31.44 in	1193 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

DT-3

Frame

917

Tap size

1 at +5% FCAN, 1 at -5% FCBN

Type

Dry Type Distribution Motor Drive Isolation Transformer

Wiring connection

318H

Performance Ratings

Frequency rating

60 Hz

Kva Rating

175 kVA

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

480Y/277 V

Temperature rise

150 °C rise

Miscellaneous

Weathershield

WS34

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - MD175E79](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)