

Eaton MD20E92ZZ

Catalog Number: MD20E92ZZ

Drive Isolation Transformer, Ventilated, Dry Type Distribution, DT-3, Three-phase, PV: 460 delta, Taps: 1 at +5% FCAN, 1 at -5% FCBN, SV: 460Y/266V, 150°C, 20 kVA, Al windings, Frame: 910S



Photo is representative

General specifications

Product Name

Eaton Open core-coil ventilated transformer

Catalog Number

MD20E92ZZ

UPC

786685197395

Product Length/Depth

14.12 in

Product Height

30 in

Product Width

20.12 in

Product Weight

224 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Recognized from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Open type core and coil assembly

Physical Attributes

Coil material

Aluminum

Design

DT-3

Frame

910S

Tap size

1 at +5% FCAN, 1 at -5% FCBN

Type

Dry Type Distribution, Drive Isolation Transformer

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

460 V

Secondary Voltage

460Y/266 V

Temperature rise

150 °C rise

Volt ampere rating

20 kVA

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - MD20E92ZZ](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia