

Eaton MD275E79FCU

Catalog Number: MD275E79FCU

Drive Isolation Transformer, Ventilated, Dry Type Distribution, DT-3, Three-phase, PV: 480 delta, Taps: 1 at +5% FCAN, 1 at -5% FCBN, SV: 480Y/277, 115°C, 275 kVA, Cu windings, Frame: 918A, uses WS34



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Motor drive isolation ventilated transformer	MD275E79FCU
	UPC
	786680061141
Product Length/Depth	Product Height
30.68 in	62.18 in
Product Width	Product Weight
31.44 in	2200 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Copper

Design

DT-3

Frame

918A

Tap size

1 at +5% FCAN, 1 at -5% FCBN

Type

Dry Type Distribution, Drive Isolation Transformer

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

480Y/277 V

Temperature rise

115 °C rise

Volt ampere rating

275 kVA

Miscellaneous

Weathershield

WS34

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - MD275E79FCU](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)