

Eaton MD27D79CU

Catalog Number: MD27D79CU

Drive Isolation Transformer, Ventilated, Dry Type Distribution, DT-3, Three-phase, PV: 480 delta, Taps: 2 at +2.5% FCAN, 2 at -2.5% FCBN, SV: 480Y/277, 150°C, 27 kVA, Cu windings, Frame: 912B, uses WS38



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Motor drive isolation ventilated transformer	MD27D79CU
	UPC
	786680067686
Product Length/Depth	Product Height
16.5 in	30 in
Product Width	Product Weight
23 in	320 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Copper

Design

DT-3

Frame

912B

Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

Type

Dry Type Distribution, Drive Isolation Transformer

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

480Y/277 V

Temperature rise

150 °C rise

Volt ampere rating

27 kVA

Miscellaneous

Weathershield

WS38

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - MD27D79CU



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia