

Eaton MD330D92XCU

Catalog Number: MD330D92XCU

Dry Type Distribution Motor Drive Isolation Transformer DT-3
Three-phase 460 DELTA 2 at +2.5% FCAN 2 at -2.5% FCBN
460Y/266V 150°C 330 kVA Copper windings 919E 428A WS35
50/60 Hz 300 hp



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Motor drive isolation ventilated transformer	MD330D92XCU
	UPC
	786680111075
Product Length/Depth	Product Height
36.23 in	75 in
Product Width	Product Weight
44.2 in	3347 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Copper

Design

DT-3

Frame

919E

Tap size

2 at +2.5% FCAN 2 at -2.5% FCBN

Type

Dry Type Distribution Motor Drive Isolation Transformer

Wiring connection

428A

Performance Ratings

Frequency rating

50-60 Hz

Kva Rating

330 kVA

Phase

Three-phase

Primary voltage

460 V

Secondary Voltage

460Y/266 V

Temperature rise

150 °C rise

Miscellaneous

Weathershield

WS35

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - MD330D92XCU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)