

Eaton MD330E94

Catalog Number: MD330E94

Drive Isolation Transformer, Ventilated, Dry Type Distribution, DT-3, Three-phase, PV: 575 delta, Taps: 1 at +5% FCAN, 1 at -5% FCBN, SV: 230Y/133V, 150°C, 330 kVA, Al windings, Frame: 919E, uses WS35



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Motor drive isolation ventilated transformer	MD330E94
	UPC
	786680339042
Product Length/Depth	Product Height
36.23 in	75 in
Product Width	Product Weight
44.2 in	2234 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

DT-3

Frame

919E

Tap size

1 at +5% FCAN, 1 at -5% FCBN

Type

Dry Type Distribution, Drive Isolation Transformer

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

575 V

Secondary Voltage

230Y/133 V

Temperature rise

150 °C rise

Volt ampere rating

330 kVA

Miscellaneous

Weathershield

WS35

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - MD330E94](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)