

Eaton MD40E92FCU

Catalog Number: MD40E92FCU

Dry Type Distribution Motor Drive Isolation Transformer DT-3
Three-phase 460 DELTA 1 at +5% FCAN 1 at -5% FCBN
460Y/266V 115°C 40 kVA Copper windings 912D 286D WS38 60
Hz 30 hp



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Motor drive isolation ventilated transformer	MD40E92FCU
	UPC
	786680111020
Product Length/Depth	Product Height
16.5 in	30 in
Product Width	Product Weight
23 in	430 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Copper

Design

DT-3

Frame

912D

Tap size

1 at +5% FCAN, 1 at -5% FCBN

Type

Dry Type Distribution Motor Drive Isolation Transformer

Wiring connection

286D

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

460 V

Secondary Voltage

460Y/266 V

Temperature rise

115 °C rise

Miscellaneous

Weathershield

WS38

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - MD40E92FCU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)