

Eaton MD63E92

Catalog Number: MD63E92

Drive Isolation Transformer, Ventilated, Dry Type Distribution, DT-3, Three-phase, PV: 460 delta, Taps: 1 at +5% FCAN, 1 at -5% FCBN, SV: 460Y/266V, 150°C, 63 kVA, Al windings, Frame: 914D, uses WS39



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Motor drive isolation ventilated transformer	MD63E92
	UPC
	786680331770
Product Length/Depth	Product Height
22 in	39 in
Product Width	Product Weight
29 in	535 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

DT-3

Frame

914D

Tap size

1 at +5% FCAN, 1 at -5% FCBN

Type

Dry Type Distribution, Drive Isolation Transformer

Performance Ratings

Frequency rating

60 Hz

Phase

Three-phase

Primary voltage

460 V

Secondary Voltage

460Y/266 V

Temperature rise

150 °C rise

Volt ampere rating

63 kVA

Miscellaneous

Weathershield

WS39

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - MD63E92](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)