

Eaton MD660E90

Catalog Number: MD660E90

Eaton 660 kVA Rating; 3-Phase; DT-3 Drive Isolation Transformer; Ventilated; 230; 575Y/332; 150 Degree C; Aluminum Windings



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Motor drive isolation ventilated transformer	MD660E90
	UPC
	786680337208
Product Length/Depth	Product Height
0.001 in	0.001 in
Product Width	Product Weight
0.001 in	0.001 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

DT-3

Tap size

1 at +5% FCAN, 1 at -5% FCBN

Type

Dry Type Distribution, Drive Isolation Transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

660 kVA

Phase

Three-phase

Primary voltage

230 V

Secondary Voltage

575Y/332 V

Temperature rise

150 °C rise

Resources

Specifications and datasheets

[Eaton Specification Sheet - MD660E90](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia