

Eaton MRI8300GY

Catalog Number: MRI8300GY

Eaton extra heavy-duty hospital grade standard duplex receptacle, MRI duplex receptacle, #14 - 10 AWG, 20A, Healthcare, Flush, 125V, Back and side, Gray, Brass, Nylon, 5-20R, Two-pole, Three-wire, Standard, Screw, Non-ferrous material



Photo is representative

General specifications

Product Name	Catalog Number
Eaton extra heavy-duty hospital grade duplex receptacle	MRI8300GY
	UPC
	032664767210
Product Length/Depth	Product Height
1.31 in	4.06 in
Product Width	Product Weight
0.88 in	0.3 lb
Certifications	
cULus Listed	
NOM	

defaultTaxonomyAttributeLabel

Device type

Duplex

Type

MRI duplex receptacle

Amperage Rating

20A

Voltage rating

125V

Contact material

Brass

Features

Non-ferrous material

Application

Healthcare

Device grade

Extra heavy-duty hospital grade

Wiring method

Back and side

Number of wires

Three-wire

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

Nylon

Color

Gray

Connection type

Screw

Allowable wire size

#14-10 AWG

Resources

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - MRI8300GY](#)

[MRI hospital grade duplex receptacle spec sheet](#)

NEMA configuration

5-20R

Design type

MRI Receptacle

Face/body material

Nylon

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)