

Eaton MV48M28T22CU

Catalog Number: MV48M28T22CU

Eaton Marine Duty Transformer, Three-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 208Y/120V, 225 kVA, Cu windings, Frame: 917, uses WS34



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	MV48M28T22CU
	UPC
	786680032226
Product Length/Depth	Product Height
30.68 in	56.17 in
Product Width	Product Weight
31.44 in	1422 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year ABS Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed

Physical Attributes

Coil material

Copper

Enclosure

NEMA 2

Frame

917

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Marine Duty Transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

225 kVA

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Miscellaneous

Weathershield

WS34

Resources

Specifications and datasheets

[Eaton Specification Sheet - MV48M28T22CU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)