

Eaton N2LPSM212222

Catalog Number: N2LPSM212222

Eaton Crouse-Hinds series Light-Pak N2LPS emergency lighting system, 50/60 Hz, 120-277 Vac input voltage, LED, Krydon fiberglass-reinforced polyester, 2 lamp heads, 12 Vdc output voltage, 28W



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Light-Pak N2LPS emergency lighting system	N2LPSM212222
	UPC
	662276806665
Product Length/Depth	Product Height
5.56 in	13.23 in
Product Width	Product Weight
10.52 in	12 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 2

Class II, Division 2

Class I, Zone 2

NEMA Rating

4X

Product specifications

Lamp type

LED

Wattage

28W

Number of lamp heads

2

Input voltage

120-277 Vac

Output voltage

12 Vdc

Frequency rating

50/60 Hz

Voltage rating

12 Vdc

Material

Krydon fiberglass-reinforced polyester

Resources

Brochures

[Crouse-Hinds series Global LED lighting portfolio](#)

[Light-Pak N2LPSM2 LED Emergency Lighting System brochure](#)

Catalogs

[Crouse-Hinds series Light-Pak N2LPS LED Emergency Lighting System catalog page](#)

Certification reports

[Light-Pak N2LPS LED Emergency Lighting System UL certification](#)

[Light-Pak N2LPS LED Emergency Lighting System Canadian certification](#)

[Light-Pak N2LPS LED Emergency Lighting System Marine certification](#)

Installation instructions

[IF 1853 - N2LPS LED Emergency Lighting System](#)

[IF 1854 - N2LPS LED Emergency Lighting System - K57](#)

Specifications and datasheets

[Eaton Specification Sheet - N2LPSM212222](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)