

Eaton N43M28T25X

Catalog Number: N43M28T25X

K-Factor Non Linear Transformer, Ventilated, K-13, Three-phase, PV: 416V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 208Y/120V, 150°C, 25 kVA, Al windings , Elec. Shield, Frame: 912B, uses WS38



Photo is representative

General specifications

Product Name	Catalog Number
Eaton K-Factor nonlinear ventilated transformer	N43M28T25X
	UPC
	786680061295
Product Length/Depth	Product Height
16.5 in	30 in
Product Width	Product Weight
23 in	268 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Type

Ventilated transformer

Design

K-13

Frame

912B

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Performance Ratings

Frequency rating

50-60 Hz

Phase

Three-phase

Primary voltage

416 V

Secondary Voltage

208Y/120 V

Temperature rise

150 °C rise

Miscellaneous

Special features

Electrostatically Shielded

Weathershield

WS38

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Eaton's Transformer Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - N43M28T25X](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)