

Eaton N48M28B49CUNV

Catalog Number: N48M28B49CUNV

Eaton K-Factor Non Linear Transformer, Non-Ventilated, K-13, Three-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 208Y/120V, 80°C, 150 kVA, Cu windings, Elec. Shield, Frame: 920NE



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Totally enclosed non-ventilated transformer	N48M28B49CUNV
	UPC
	786680093845

Product Length/Depth	Product Height
35.75 in	75 in

Product Width	Product Weight
44.46 in	4160 lb

Warranty	Certifications
-----------------	-----------------------

Eaton Selling Policy 25-000, one (1) year UL Listed

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

[Catalog Notes](#)

Totally enclosed non-ventilated



Powering Business Worldwide

Physical Attributes

Coil material

Copper

Design

K-13

Frame

920NE

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Non-ventilated transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

150 kVA

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Temperature rise

80 °C rise

Miscellaneous

Special features

Electrostatically Shielded

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - N48M28B49CUNV](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)