

Eaton N48M28T15CUNV

Catalog Number: N48M28T15CUNV

K-Factor Non Linear Transformer, Non-Ventilated, K-13, Three-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 208Y/120V, 150°C, 15 kVA, Cu windings, Elec. Shield, Frame: 912BN



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Totally enclosed non-ventilated transformer	N48M28T15CUNV
	UPC
	786680071317
Product Length/Depth	Product Height
16.5 in	30 in
Product Width	Product Weight
23 in	415 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Totally enclosed non-ventilated

Physical Attributes

Coil material

Copper

Design

K-13

Frame

912BN

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Non-ventilated transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

15 kVA

Phase

Three-phase

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Temperature rise

150 °C rise

Miscellaneous

Special features

Electrostatically Shielded

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - N48M28T15CUNV](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)