

Eaton NCGB2234

Catalog Number: NCGB2234

Eaton Crouse-Hinds series NCGB cord grip, Cable range min/max: 0.64-0.78", Non-armoured and tray cable, Non-armoured gland, Thermoplastic polyester, General purpose, 3/4" NPT



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series NCGB cord grip	NCGB2234
	UPC
	782274275918
Product Length/Depth	Product Height
3.17 in	1.38 in
Product Width	Product Weight
1.38 in	0.17 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

3

4X

Product specifications

Protection type

General purpose

Cable type

Tray cable

Non-armoured

Gland type

Non-armoured

Thread Size

3/4"

Thread type

NPT

Cable range (min/max)

0.64-0.78"

Material

Thermoplastic polyester

Resources

Catalogs

[Crouse-Hinds series NCG and NCGB catalog page](#)

Certification reports

[NCG, NCGB and NCGS Non-metallic Portable Cord Connectors UL certification](#)

[NCG, NCGB and NCGS Non-metallic Portable Cord Connectors Canadian certification](#)

Installation instructions

[IF 962 - NCGB Cord and Cable Fittings](#)

Specifications and datasheets

[Eaton Specification Sheet - NCGB2234](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)